

EMR1051 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

Designed for loaders, the EMR1051 range is the best solution for intensive loading applications in industries such as open pits and quarries as well as infrastructure and building construction and landscaping where traction cannot be compromised.

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability. The multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Main Benefits

- Optimal traction
- Excellent tire life due to deep tread
- · Cut resistant compound
- Sidewall rubber ring guard protection
- Robust carcass to support eventual retreading*












RIDE COMFORT


EMR1051

PREMIUM RADIAL PNEUMATIC



Superior tire technology for severe applications
















Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth [mm]	Service description LI/SS Loader	Tire Load Capacity (kg) 10 (km/h)	Tire Pressure (bar)
20.5 R 25	L5	17.00/2.0-25 (17.00/1.7-25)	70	** 193 A2	11,500	5.75
23.5 R 25	L5	19.50/2.5-25	76	** 201 A2	14,500	5.75
26.5 R 25	L5	22.00/3.0-25	85	** 209 A2	18,500	5.75
29.5 R 25	L5	25.00/3.5-25	92	** 216 A2	22,400	5.75

^{** -} Index of tire strength















www.trelleborg-tires.com