



ST-3000

RESILIENT - HIGH INTENSITY APPLICATIONS

Main Benefits

- **Block tread design**
Large footprint lowers stress and maximizes tire life.
- **Wear resistant technology**
Less downtime and increased value.
- **Shock absorbance**
Tire absorbs shock from obstacles.
- **Rim security**
Rim protection from accidental damage and anti slip bead wires.
- **Enhanced stability**
Faster load positioning and cornering.
- **Energy efficiency**
Low rolling resistance for improved energy efficiency.

Polymer Engineering, Application Expertise

Trelleborg strives to deliver optimum performance for all our customers. We offer problem-solving products in our premium range. Contact our application specialists to learn more about our latest tire solutions.



STABILITY



TIRE LIFE



BATTERY LIFE



OVERHEATING TIRE



VIBRATION



TIRE CRACKING



EXPLOSION RISK



TIRE CHUNKING

Special compounds available



ST-3000

RESILIENT - HIGH INTENSITY APPLICATIONS

Tire Size	Alternative Size	Rim	Tread Pattern	LOC	Tire Dimensions [mm]		Tire Load Capacity [kg]				
					Section Width	Overall Diameter	Forklift trucks up to 25 km/h		Other Vehicles [kg]		
							Load Wheel	Steer Wheel	6 km/h	10 km/h	25 km/h
5.00-8		3.00-8	ST3		124	447	1415	1090	1415	1285	1090
5.00-8		3.25-8	ST3		124	447	1415	1090	1415	1285	1090
18x7-8	(180/70-8)	4.33R-8	ST3	●	145	452	2145	1650	2145	1945	1650
16x6-8	(150/75-8)	4.33R-8	ST3	●	140	406	1455	1120	1455	1320	1120
15x4.5-8	(125/75-8)	3.00R-8	ST3	●	111	375	1040	800	1040	945	800
140/55-9		4.00R-9	ST3	●	131	379	1170	900	1170	1060	900
18x7-8	(180/70-8)	3.00R-8	ST3		145	452	2145	1650	2145	1945	1650
23x9-10	(225/75-10)	6.50R-10	ST3	●	199	565	3445	2650	3445	3125	2650
23x9-10	(225/75-10)	5.00R-10	ST3		199	565	3445	2650	3445	3125	2650
23x10-12	(250/60-12)	8.00R-12	ST3	●	245	575	3770	2900	3770	3420	2900
21x8-9		6.00R-9	ST3	●	190	524	2755	2120	2755	2500	2120
200/50-10		6.50R-10	ST3	●	194	450	2470	1900	2470	2240	1900
27x10-12		8.00R-12	ST3	●	247	660	3900	3000	3900	3540	3000
6.00-9		4.00E-09	ST3	●	137	525	1885	1450	1885	1710	1450
6.50-10		5.00F-10	ST3	●	151	569	2340	1800	2340	2125	1800
7.00-12		5.00S-12	ST3	●	169	657	2910	2240	2910	2645	2240
28x12.5-15	(355/45-15)	9.75-15	ST3	●	292	683	5040	3875	5040	5945	5040
28x9-15		7.0-15	ST3	●	206	690	3770	2900	3770	3420	2900
7.00-15		5.5-15	ST3	●	168	714	3545	2725	3545	3215	2725
7.00-15		6.0-15	ST3	●	168	714	3545	2725	3545	3215	2725
8.25-15		5.5-15	ST3		208	805	4745	3650	4745	4305	3650
8.25-15		6.5-15	ST3	●	208	805	4745	3650	4745	4305	3650
8.25-15		6.5-15	ST3/LISO		223	807	4745	3650	4745	4305	3650
250-15	(250/70-15)	7.5-15	ST3	●	210	709	4745	3650	4745	4305	3650
250-15	(250/70-15)	7.0-15	ST3	●	210	709	4745	3650	4745	4305	3650
300-15		8.0-15	ST3	●	251	809	5850	4500	5850	5310	4500
350-15	(355/65-15)	9.75-15	ST3	●	300	813	7800	6000	7800	7080	6000



Follow us



Yokohama TWS S.p.A.
Via Nazionale Tiburtina, 143 - 00019 Villa Adriana - Tivoli (RM), Italy
Phone: +39 0774 3841 – info.tws@yokohama-tws.com
www.trelleborg-tires.com

