



## T-800

BIAS PNEUMATIC - MEDIUM INTENSITY APPLICATIONS

### Main Benefits

- **Block tread design**  
Large footprint lowers stress and maximizes tire life.
- **Enhanced stability**  
Faster load positioning and cornering.
- **Shock absorbance**  
Tire absorbs shock from obstacles.
- **Energy management system**  
Keeps the internal temperature low ensuring maximum uptime.

### Polymer Engineering, Application Expertise

Trelleborg strives to deliver optimum performance for all our customers. We offer problem-solving products in our premium range. Contact our application specialists to learn more about our latest tire solutions.



STABILITY



TIRE LIFE



TIRE OVERHEATING



PUNCTURE RESISTANCE

# T-800

BIAS PNEUMATIC - MEDIUM INTENSITY APPLICATIONS

## TREAD PATTERNS



T-800

Size	Alternative Size	Ply Rating	Rim	Product Dimensions [mm]			Inflation Pressure [bar]	Tire Type	Load Index	Speed Symbol	Load Capacity [kg]	
				Overall Diameter	Section Width	Tread Depth					Counterbalanced Lift Trucks up to 25 km/h	
											Load Wheel	Steering Wheel
<b>15x4½-8</b>	125/75-8	12	3.25-8	385	122	8	10.00	Tube Type	100	A5	1,040	800
<b>18x7-8</b>	180/70-8	16	4.33R-8	453	160	17	10.00	Tube Type	125	A5	2,145	1,650
<b>5.00-8</b>		10	3.00D-8	465	135	13	10.00	Tube Type	111	A5	1,415	1,090
<b>21x8-9</b>	200/75-9	14	6.00E-9	536	204	18	9.00	Tube Type	131	A5	2,535	1,950
<b>6.00-9</b>		12	4.00E-9	540	155	13	10.00	Tube Type	121	A5	1,885	1,450
<b>23x9-10</b>	225/75-10	20	6.50F-10	585	228	19	10.00	Tube Type	142	A5	3,445	2,650
<b>6.50-10</b>		10	5.00F-10	597	183	14	7.80	Tube Type	122	A5	1,950	1,500
<b>7.00-12</b>		14	5.00S-12	685	196	15	9.00	Tube Type	134	A5	2,755	2,120
<b>27x10-12</b>	250/75-12	14	8.00G-12	691	245	21	7.00	Tube Type	143	A5	3,545	2,725
<b>28x9-15</b>	225/75-15 (8.15-15)	14	7.0-15	722	217	20	10.00	Tube Type	146	A5	3,900	3,000
<b>7.00-15</b>	29x8-15	14	5.5-15	755	190	17	9.30	Tube Type	140	A5	3,250	2,500
<b>250-15</b>	250/70-15	20	7.0-15	760	240	21	10.30	Tube Type	155	A5	5,040	3,875
<b>7.50-15</b>		14	6.0-15	808	215	17	9.30	Tube Type	144	A5	3,640	2,800
<b>8.25-15</b>		14	6.5-15	834	255	18	8.00	Tube Type	149	A5	4,225	3,250
<b>300-15</b>	315/70-15	20	8.0-15	840	290	25	9.40	Tube Type	164	A5	6,500	5,000



Follow us



Yokohama TWS S.p.A.  
Via Nazionale Tiburtina, 143 - 00019 Villa Adriana - Tivoli (RM), Italy  
Phone: +39 0774 3841 – info.tws@yokohama-tws.com  
www.trelleborg-tires.com

