


Fluid transfer solutions
Industrial hoses / New range
www.trelleborg.com/fluidhandling

♣ Gericulture & Forestry



		H		
Water delivery hose used for the discharge of industrial water, waste water and agricultural equipment.	51-305	5	-	- 30/+ 80 °C
Water delivery hose used for the discharge of industrial water, waste water and agricultural equipment.	25-305	10	-	- 30/+ 80 °C
Water delivery hose used for the discharge of industrial water, waste water and agricultural equipment.	25-203	20-18	-	- 30/+ 80 °C
Water suction and delivery hose used for industrial water, waste water and agricultural equipment.	25-254	10	0.9	- 30/+ 80 °C
Hot water delivery hose used in industry, construction and agricultural applications.	25-152	10	-	- 30/+ 100 °C
Hot water suction and delivery hose used in industry, construction and agricultural applications.	25-254	10	0.9	-30/+100 °C
Heavy duty water delivery hose for tough applications in industry, agriculture and constructions sites.	25-152	10	-	- 30/+ 80 °C






CHEM 16 UPE SD EN 12115

AQUA 10 INDUS





Chemical resistant suction and delivery hose.

19-102 16 0.9 -30/+100 °C

0.9

10

-30/+100 °C



TRELLEBORG


TRELLEBORG

TRELLEBORG

Oil & Gas



OIL 10



STEAM 6 / Low pressure steam hose.	19-51	6	-	-30/+164 °C
STEAM 16 RED / High pressure steam hose.	13-51	16	-	-30/+210 °C
STEAM 16 / High pressure steam hose.	13-51	16	-	-30/+210 °C
Mineral and synthetic oil and household fuel delivery hose (with aromatic content up to 50%).	16-102	10	-	-30/+80 °C
Mineral and synthetic oil and household fuel suction and delivery hose (with aromatic content up to 50%).	19-152	10	0.9	-30/+80 °C

13-102





Delivery hose to transfer abrasive material such as cement, sand, etc.	75-152	7	-	- 30/+ 80 °C	
Suction and delivery hose to transfer abrasive material such as cement, sand, etc.	76-152	10	0.9	- 30/+ 80 °C	
Abrasive food material delivery hose for food industry such as grain, PVC granules.	75-127	7	-	- 30/+ 80 °C	




19-102

21-2.5

0.9

-40/+100 °C



SAE 100R4

Trelleborg is a world leader in engineered polymer solutions that seal, damp and protect critical applications in demanding environments. Its innovative solutions accelerate performance for customers in a sustainable way.

WWW.TRELLEBORG.COM