

## Floating Fenders Project Requirements

TYPE OF FLOATING FENDER			
Pneumatic: 50kPa 80kPa	☐ Foam filled		
DATE REQUIRED	QUANTITY OF UNITS REQUIRED		
TYPE OF AGREEMENT			
Purchase	Rental		
IF RENTAL, HIRE AGREEMENT IN PLACE			
□Yes	□No		
IF RENTAL, DURATION OF RENTAL IN DAYS			
DELIVERY / COLLECTION LOCATION			
☐ Self collection from Trelleborg base	☐ Port of delivery, please specify:		
FENDER BODY SIZE REQUIRED	TYPE OF APPLICATION		
TYPE OF CHAIN TYRE NET			
□Lorry	Aircraft		
RIGGING REQUIRED			
Lifting sling	☐ Chain and shackles		
Mooring rope: Alongside ietty ( meters) Alongside barge ( meters) Alongside vessel ( meters)			



## **SERVICES**

FENDER INSPECTION				
☐ In-house		☐ At client's location		
RE-NETTING OF FENDERS				
☐ Aircraft tyre		☐ Lorry tyre		
FENDER MOORING				
Required		☐ Not required		
TYPE OF MOORING				
☐ Wire rope ☐ chain ☐ mooring rope	Length per section:		Fitting: Soft Eye Hard Thimble	
DISPOSAL OF FENDER				
☐ Fender body disposal		☐ Fender body & net disposal		
FENDER INFLATION SERVICE				
Required		☐ Not required		
TRANSPORTATION				
☐ By Trelleborg		☐ By client		
You may send in your project requirements to: marine_infra@trelleborg.com				