

epros® DrainPacker Patch Kit

01

Configuration pack:	No. 01	234462
Main pipe:	4"	
Rehabilitation length:	2 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1,
1 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

02

Configuration pack:	No. 02	234468
Main pipe:	4"	
Rehabilitation length:	4 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

03

Configuration pack:	No. 03	234463
Main pipe:	6"	
Rehabilitation length:	2 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1, 1½ liter bag
- 1 PCS epros® FibreGlassMat CRF(+) 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



Configuration pack:	No. 04	234469
Main pipe:	6"	
Rehabilitation length:	4 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1, 1 liter bag
- 1 PCS epros® Silicate Resin Type W1, 2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+) 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

05

Configuration pack:	No. 05	234464
Main pipe:	8"	
Rehabilitation length:	2 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

06

Configuration pack:	No. 06	234470
Main pipe:	8"	
Rehabilitation length:	4 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 2 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

07

Configuration pack:	No. 07	230100
Main pipe:	8"	
Rehabilitation length:	5 ft	
Resin type:	Silicate S1	
Pot time:	32 min, 68 °F	
Cure time:	260 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type S1, 1 liter bag
- 1 PCS epros® Silicate Resin Type S1, 2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+) 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

08

Configuration pack:	No. 08	234502
Main pipe:	8"	
Rehabilitation length:	5 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1,
1 liter bag
- 2 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

09

Configuration pack:	No. 09	234465
Main pipe:	10"	
Rehabilitation length:	2 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1, ½ liter bag
- 1 PCS epros® Silicate Resin Type W1, 2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+) 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

10

Configuration pack:	No. 10	234471
Main pipe:	10"	
Rehabilitation length:	4 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1, 1 liter bag
- 2 PCS epros® Silicate Resin Type W1, 2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+) 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



Configuration pack:	No. 11	234466
Main pipe:	12"	
Rehabilitation length:	2 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 1 PCS epros® Silicate Resin Type W1,
1 liter bag
- 1 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

12

Configuration pack:	No. 12	234472
Main pipe:	12"	
Rehabilitation length:	4 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 3 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

13

Configuration pack:	No. 13	234467
Main pipe:	15"	
Rehabilitation length:	2 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 2 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.



epros® DrainPacker Patch Kit

14

Configuration pack:	No. 14	234473
Main pipe:	15"	
Rehabilitation length:	4 ft	
Resin type:	Silicate W1	
Pot time:	15 min, 68 °F	
Cure time:	115 min, 59 °F	

Contents:

- 4 PCS epros® Silicate Resin Type W1,
2 liter bag
- 1 PCS epros® FibreGlassMat CRF(+)
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

Made in the EU.

Please read our Safety Data Sheets.

