

Key Performance

- Ideal for 3-piece can printing
- Extreme high printing quality
- Compatible with conventional inks.

MAIN APPLICATION

Metal Decorating

**Printec 814 is available in 3 ply
(1,98 mm) thickness**



Printec 814



The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Red
THICKNESS (mm)	1,98
AVERAGE LOAD VALUE N/cm2 @ 0,20 mm Indentation	125
SURFACE ROUGHNESS (µm)	0,70 to 1,30
ELONGATION (%)	< 2
TENSILE STRENGTHS (kgf/cm)	> 71.5
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
APPLICATIONS	Metal Decorating

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printing@trelleborg.com**