



Rollin® UV-E




Key performance

- Specifically designed for UV applications
- Excellent half tone production
- Excellent smash resistance
- Suitable for packaging and metal decorating applications
- Sticky back blanket

MAIN APPLICATION

Commercial Sheetfed,
Packaging, Metal Decorating

**Rollin UV-E available in 3 ply,
1,71/1,96 mm thickness.**




Rollin UV-E

✓ The product at a glance

INK COMPATIBILITY	UV
PRINTING SURFACE COLOUR	Green
THICKNESS (mm)	1,71/1,96
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	0,8
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
CARCASS CONSTRUCTION	High uv chemical resistance

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**