

vulcan[®] Sprint

Key performance

- Sticky back blanket
- Very flexible and soft carcass for easy mounting
- High print quality
- Very versatile: suitable for labels & envelopes printing
- Adhesive: clean and easy removal from the cylinder

MAIN APPLICATION

Business Forms, Labels

Vulcan Sprint is available in 1 ply,
0,90 - 0,95 - 1,00 - 1,05 mm
thickness



Vulcan Sprint

✓ The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Blue
THICKNESS(mm)	0,90 - 0,95 - 1,00 - 1,05
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	0,8
ADDITIONAL INFORMATION	
APPLICATIONS	Business Forms and Labels

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**