



UV LIGHT LED curing



LED CURING SYSTEM FOR LATERALS

LED-curing the easy way. One system for LED light curing with only one head for laterals and small main sewers.

With intense UV-light and innovative cooling technique, the light-head ensures fully cured liners, every time. The slim body design and compact light-unit, enables the head to pass through the otherwise impossible, 90 degree bends.

With a camera and LED on the top of the head, you can easily inspect your installation right before curing, without the need of a separate inspection unit. This eliminates back jobs due to curing of collapsed liners.

Field of application:

- Pipes and sewers from DN 70 to DN 300

Light source:

- 5 x 110 W LED lamps with quartz glass

Cable length:

- 70 m push rod (230 ft)

Bendability:

- Bendable 90° from DN 70

Dimensions:

- 900 x 550 x 1590 mm (L x W x H)



DISCOVER OUR
LARGE SELECTION OF
MATCHING UV RESINS
AND LINERS



TRELLEBORG