

QUICK RELEASE HOOKS & CAPSTAN SPECIFICATIONS ENQUIRY

Company:	Phone:
Contact Person:	Fax:
Office Location:	Email:
Project Reference:	
Commercial Port/Shipping Destination:	Date:

Hook Size (Tonnes)	State No. of Units Required								Proof Load 150% or 125%
	Single	Double	Triple	Quadruple	Back to Back	With Ex'd' Capstan	With Non Ex'd' Capstan	Without Capstan	
45									
60									
75									
100									
125									
150									
Other									

Type of Facility:

Oil <input type="checkbox"/>	Gas <input type="checkbox"/>	Product <input type="checkbox"/>	Bulk <input type="checkbox"/>	Other <input type="checkbox"/>
------------------------------	------------------------------	----------------------------------	-------------------------------	--------------------------------

Zoning:

Non-Hazardous Area <input type="checkbox"/>	Hazardous Area <input type="checkbox"/>	Both Hazardous & Non- Hazardous (specify which hook units) <input type="checkbox"/>
---	---	--

Foundation:

Concrete (Standard) <input type="checkbox"/>	Steel (Bolt Down Base) <input type="checkbox"/>	Steel (Weld Down Base) <input type="checkbox"/>
--	---	---

Remote Release System:

Not Required <input type="checkbox"/>	Required – Electrical <input type="checkbox"/>	Required – Hydraulic <input type="checkbox"/>	Future Requirement <input type="checkbox"/>
---------------------------------------	--	---	---

Load Monitoring System:

Required <input type="checkbox"/>	Not Required <input type="checkbox"/>	Future Requirement <input type="checkbox"/>
-----------------------------------	---------------------------------------	---

Power Supply:

Specify Voltage 3 Phase: V	Specify Voltage Single Phase: V	Specify Frequency: Hz
---------------------------------	--------------------------------------	----------------------------

Line Pull Capacity (Tonnes):

1.0 <input type="checkbox"/>	1.5 <input type="checkbox"/>	2.0 <input type="checkbox"/>	3.0 <input type="checkbox"/>
------------------------------	------------------------------	------------------------------	------------------------------

Line Speed (meters per minute):

30 (standard) <input type="checkbox"/>	Other <input type="checkbox"/>
--	--------------------------------

Operation:

Reversible with brake (Standard) <input type="checkbox"/>	Non-reversible with back-stop bearing <input type="checkbox"/>
---	--

Options:

Hooks Insulated from Jetty Required <input type="checkbox"/>	Not Required <input type="checkbox"/>
---	---------------------------------------

OTHER REQUIREMENTS – PLEASE SPECIFY

.....

.....

.....

This enquiry form describes alternatives within the manufacturer's standard product range. Please attach an equipment specification, if available.