

ALCODIAL

AGRI & FOOD

Foodstuff transfer



Applications

Particularly adapted for alcohol transfer up to 99 %.
Suitable for all drinks: wine, beer, fruit juice, milk, etc.
Designed for equipment of:
- production plants (distillery, spirit and liqueur producer, etc) ;
- loading or unloading bays from road and rails tankers.

Advantages

- Very flexible and anti-kinking resistant hose.
- UPE inner tube accepting alcohol temporary stagnation without risk of migration.
- Odourless and tasteless inner tube.
- Non-marking, abrasion resistant cover.
- Contains no phthalate.

Technical description

Inner tube: food grade UPE, white, smooth.
Reinforcement: synthetic textile with embedded steel helix.
Cover: NR, blue, fabric impression.
Temperature range: - 30 °C to + 80 °C.
Standard/Approval:
EU regulations n° 1935/2004 and 2023/2006.
FDA regulation 21 CFR 177.1520.
French legislation.

All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

ALCODIAL

26/07/2010

ID	OD	Working pressure	Bursting pressure	Max vacuum	Bending radius	Weight	Length	Article number	Stock (■) or min. order
mm	mm	bar	bar	bar	mm	kg/m	m		m
25.0	-0/+1 36.0 ±1.0	6	18	0.9	55	0.70	20	5501078	■
							40	5501079	■
32.0	-0/+1 43.0 ±1.0	6	18	0.9	70	0.82	20	5501080	◇
							40	5501081	■
38.0	-0/+1 49.0 ±1.0	6	18	0.9	84	1.13	20	5501082	■
							40	5501083	■
51.0	-0/+1 62.5 ±1.5	6	18	0.9	112	1.76	20	5501084	■
							40	5501085	■
63.0	-0/+1 74.5 ±1.5	6	18	0.9	139	2.08	20	5501086	◇
							40	5501087	■
70.0	-0/+1 83.0 ±1.5	6	18	0.9	154	2.54	20	5501088	■
							40	5501089	■
76.0	-0/+1 89.0 ±1.5	6	18	0.9	167	2.94	20	5501090	◇
							40	5501091	■

Branding

◇ Upon availability.



and embossed: TRELLEBORG - ALCODIAL - ND - WP 6 bar - week/year - Made in France

