

# BIOCLEAN

## AGRI & FOOD

Cleaning in food environment



### Applications

High pressure cleaning specifically for food industries.  
Can also be used for transfer of any liquid foodstuffs.

### Advantages

- Very flexible.
- Non-marking cover.
- Food grade quality white inner tube, oil resistant.
- Branding over red stripe for easy and quick identification.
- Contains no phthalate.

### Technical description

**Inner tube:** food grade quality, oil resistant NBR, white, smooth.

**Reinforcement:** synthetic textile.

**Cover:** oil and weather resistant NBR/PVC, blue, smooth.

**Temperature range:** - 20 °C to + 100 °C.

**Standard/Approval:**

EU regulation n° 1935/2004 and 2023/2006.

FDA regulation 21 CFR 177.2600.

German legislation: BfR recommendation XXI cat. 3.

French legislation.

All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

### Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

## BIOCLEAN

13/07/2010

ID	OD	Working pressure	Bursting pressure	Bending radius	Weight	Length	Article number	Stock (■) or min. order		
mm	mm	bar	bar	mm	kg/m	m		m		
<b>7.9</b>	± 0.5	15.9	± 0.6	60	180	50	0.20	20	5026076	◇
								40	5026077	◇
								80	5026078	◇
								120	5026109	■
<b>9.5</b>	± 0.5	18.0	± 0.7	60	180	60	0.25	20	5026110	◇
								40	5026113	◇
								80	5026114	◇
								120	5026115	■
<b>12.7</b>	± 0.6	22.0	± 0.8	60	180	70	0.34	20	5012778	◇
								40	5012779	■
								80	5026111	■
								120	5026112	■
<b>15.9</b>	± 0.8	26.5	± 1.0	60	180	80	0.48	20	5026079	◇
								40	5026080	◇
								80	5026081	◇
								120	5026116	■

◇ Upon availability.

### Branding



and embossed: month/year

