

CALIKLER HT

CONSTRUCTION & ENVIRONMENT

Air line



Applications

Air line from compressor/booster on all types of tanker lorries for bulk transport of powdered products.

Advantages

- Extremely flexible with very low bending radius.
- Suitable for all types of road tanker compressors/boosters.
- Can be supplied fitted with swaged couplings, conforming with transported materials specifications.

Technical description

Inner tube: heat resistant EPDM, white, smooth.

Reinforcement: high temperature resistant textile with embedded steel helix.

Cover: weather resistant EPDM, black, fabric impression.

Temperature range: - 30 °C to + 180 °C (peaks at + 240 °C).

CALIKLER HT

08/07/2010

ID	Wall thickness		OD		Working pressure	Bursting pressure	Max vacuum	Bending radius	Weight	Length	Article number	Stock (■) or min. order
mm	mm	mm	mm	mm	bar	bar	bar	mm	kg/m	m		m
50.0	7.0	±1	64.0	±1.5	3	18	0.8	125	1.81	20	0060213	■
										40	0060212	■
55.0	6.5	±1	68.0	±1.5	3	18	0.8	140	1.84	20	0200589	120
										40	0200588	120
60.0	6.5	±1	73.0	±1.5	3	18	0.8	150	1.98	20	0070666	120
										40	0070667	120
70.0	7.0	±1	84.0	±1.5	3	18	0.8	210	2.63	20	0200591	■
										40	0200590	120
75.0	7.5	±1	90.0	±1.5	3	18	0.8	225	2.96	20	0060215	■
										40	0060214	■
89.0	7.0	±1	103.0	±1.5	3	18	0.8	310	3.26	20	0200593	■
										40	0200592	120

Branding

