

# SABLEX



## CONSTRUCTION & ENVIRONMENT Evacuation and material handling hoses

### Applications

For cleaning and shot blasting castings, metal, stone, and concrete surfaces.

### Advantages

- Small tolerances, therefore easy to couple.
- Longitudinally stable i.e. the length will not alter under pressure (unstable hoses result in the operator losing control when pressure is applied).
- Light weight and flexible for easy handling.
- Conductive inner tube compound gives increased safety for the operator, since there is no risk of wire breakage in use.

### Technical description

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: - 30 °C to + 70 °C.

Electrical properties: conductive tube,  $R < 2.10^6 \Omega/m$ .

Special properties: abrasion resistance of tube  $< 70 \text{ mm}^3$  according to DIN 53 516

## SABLEX

29/07/2011

ID mm	Wall thickness mm		OD mm		Working pressure bar	Bursting pressure bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
13	7.0	± 0.50	27.0	± 1.0	12.0	40	65	0.58	20	0028711	■
									40	0060061	■
16	7.0	± 0.50	30.0	± 1.0	12.0	40	80	0.68	20	0028719	400
									40	0028720	400
19	7.5	± 0.50	34.0	± 1.0	12.0	40	100	0.78	20	0028745	■
									40	0028746	■
25	7.0	± 0.50	39.0	± 1.0	12.0	40	125	0.86	20	0060969	■
									40	0060970	■
32	8.0	± 0.50	48.0	± 1.0	12.0	40	160	1.3	20	0060971	■
									40	0060972	■
									20	0070785	400
									40	0070786	200
35	9.0	± 0.50	53.0	± 1.0	12.0	40	190	1.57	40	0070788	200
38	10.0	± 0.50	58.0	± 1.0	12.0	40	170	1.89	20	0070789	200
									40	0070790	■
40	10.0	± 0.50	60.0	± 1.0	12.0	40	180	1.97	20	0028786	600
									40	0028787	■
42	9.0	± 0.50	60.0	± 1.0	12.0	40	240	1.81	20	0070791	200
									40	0070792	200
50	10.0	± 0.75	70.0	± 1.5	12.0	40	250	2.36	20	0060973	■
									40	0060974	■
63	10.0	± 0.75	83.0	± 1.5	12.0	40	325	2.9	40	0060077	160
65	10.0	± 0.75	85.0	± 1.5	12.0	40	320	2.95	20	0070797	200
									40	0070798	200
76	10.0	± 0.75	96.0	± 1.5	12.0	40	400	3.42	20	0028851	■
									40	0070784	120
102	10.0	± 0.75	122.0	± 1.5	10.0	40	550	4.4	20	0028859	■
									40	0028860	80

■ Upon availability.

### Branding

