

# TRELLOIL D EC

CHEMICAL PETROCHEMICAL  
Oil and petroleum/Oil cargo hoses



## Applications

Transfer of petroleum products with aromatic content up to 50 % in large diameters.

## Advantages

- Highly robust and flexible.
- Cover particularly resistant to hydrocarbons, abrasion, atmospheric conditions, and ozone.
- Electrical conductivity fully assured by the inner tube compound.

## Technical description

Inner tube: oil and petrol resistant NBR, black, smooth.

Reinforcement: synthetic textile.

Cover: oil and weather resistant CR, black, fabric impression.

Temperature range: - 40 °C to + 100 °C.

Electrical properties: conductive tube,  $R < 10^6 \Omega/\text{lg}$ .

## Complementary information

Can be delivered with swaged-on standard steel flanges (PN 10, PN 16, PN 20). Please consult us for any other type of ends or delivery lengths.

# TRELLOIL D EC

09/01/2012

ID mm	OD mm	Working pressure bar	Bursting pressure bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
100 ± 1.5	118.0 ± 1.5	20.0	60	600	4.15	40	5513112	1600
125 ± 1.5	143.0	20.0	60	750	5.04	40	5513113	1600
150 ± 1.5	170.0 ± 1.5	20.0	60	900	6.5	40	5513114	1600
204 ± 1.5	227.5 ± 1.5	20.0	60	1400	9.63	40	5513115	1600
251 ± 2.0	274.0 ± 2.2	20.0	60	1800	11.67	40	5513116	1600

## Branding



and embossed: TRELLEBORG · TRELLOIL D EC · ND · WP 20 bar · BP 60 bar · Ω · month/year · batch number · Made in France

