

TRELLVAC Transporter HD



CONSTRUCTION & ENVIRONMENT Evacuation and material handling hoses

Applications

Transport hose for vacuum cleaning trucks and in stationary systems in straight or bend positions in all types of industries. Extraction and transport of abrasive materials such as sand, gravel, stone, sludge and powder.

Advantages

- n Fully rot resistant reinforcement.
- n Smooth cover.
- n Flexible and very high abrasion resistance.
- n Can be used for vacuum and discharge.

Technical description

Inner tube: wear resistant NR/SBR, black, smooth.
 Reinforcement: synthetic textile cords with embedded steel helix.
 Cover: wear and weather resistant SBR, black, fabric impression.
 Temperature range: - 40 °C to + 90 °C.
 Electrical properties: conductive tube and cover, $R < 10^6 \Omega/m$, and built-in conductive wire.



Resistance ●●●●●●

Flexibility ●●●●○

Weight ●●●●○

TRELLVAC Transporter HD

21/11/2011

ID mm	OD mm	Working pressure bar	Bursting pressure bar	Max. vacuum bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
51 ± 1.5	64.0 ± 1.0	5.0	15	0.9	210	1.8	20	5500753	120
							40	5500752	n
63 ± 1.5	76.0 ± 1.0	5.0	15	0.9	250	2.2	20	5500755	120
							40	5500754	n
76 ± 1.5	90.0 ± 1.5	5.0	15	0.9	300	2.8	20	5500757	160
							40	5500756	n
90 ± 1.5	104.0 ± 1.5	5.0	15	0.9	350	3.4	20	5500759	120
							40	5500758	n
102 ± 1.5	117.0 ± 1.5	5.0	15	0.9	400	3.8	20	5500761	160
							40	5500760	n
108 ± 1.5	123.0 ± 2.0	5.0	15	0.9	430	4.1	20	5500763	120
							40	5500762	n
116 ± 1.5	131.0 ± 2.0	5.0	15	0.9	450	4.6	20	5500765	120
							40	5500764	n
127 ± 1.5	143.0 ± 2.0	5.0	15	0.9	510	5.3	20	5500767	n
							40	5500766	n
140 ± 1.5	156.0 ± 2.0	5.0	15	0.9	580	5.7	20	5500769	40
							40	5500768	40
152 ± 1.5	168.0 ± 2.0	5.0	15	0.9	640	6.3	20	5500771	n
							40	5500770	n
165 ± 1.5	182.0 ± 2.0	3.0	10	0.9	700	7.2	10	5500772	40
204 ± 1.5	222.0 ± 2.0	3.0	10	0.9	820	9.9	10	5501132	n

Branding

