



EDITOR 10

Description

Whit neutral feeding characteristics Editor 10 is the neutral feeding version of the editor series.

the Vulcan Editor is especially designed for high speed newspaper presses, Vulcan Editor combines excellent rebound with damping characteristics with absorb mechanical vibration.

MAIN APPLICATION

Newspaper

Vulcan Editor 10 is available in 3-ply, (1.96 mm) thickness.



Standard



Vulcan Editor 10

✓ The product at a glance

COLOUR	Dark Blue
THICKNESS (mm)	1,96 (no pak)
SOURFACE ROUGHNESS(Ra micron)	1,0
INK COMPATIBILITY	Hybrid
ELONGATTION (%)	<0,9
TENSILE STRENGHT (N/mm)	>60
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	250
PAPER FEEDING	Neutral
WATER SOLVENT PROTECTED	Yes
NEW TECHNOLOGIES	Dynatech feed
ADDITIONAL INFORMATION	
SPECIAL COMPRESSIBLE LAYER	Very special compressible layers with Dynatech technology, which gives a hightolerance at the infeed unit: Lower force at infeed unit, means less risk of paper breaks. Suitable for those presses whitout in-feed or out-feed (old presses). Having a suitable paper tension, the register can be reached quickly and with less copies printed.
NO PAK VERSION	Available

**IF YOU WOULD LIKE TO SPEAK TO SOMEONE ABOUT THIS PRODUCT OR ANY OTHER VULCAN PRODUCT PLEASE SPEAK TO ONE OF OUR DEDICATED TEAM:
T: +39 0371 406.1 | printing@trelleborg.com**