



Twin Forestry. The Pure Quality Solution.



Twin Forestry

SIZE	Tread Pattern	LI/SS PR				New Tyre		Tyre in Service		SLR mm	RC mm	SRI mm	Rim	Tube
		ROAD	PR	FOREST HT	FOREST LT	SW mm	OD mm	SW (max) mm	OD (max) mm					
400/60-15.5 TT	T404 FS		14			400	875	436	907		2620	405	AG13.00	400/60-15.5
500/45-22.5 TT	T404 FS	129A8	12	129A8	136A2	500	1020	525	1045		3066	485	AG16.00	500/45-22.5
500/60-22.5 TT	T421 SB	144A8	16	144A8	151A2	500	1170	525	1200		3525	550	AG16.00	500/60-22.5
600/50-22.5 LS2 TT	T428 SB	149A8	16	149A2	156A2	600	1170	630	1199	550	3510	550	AG20.00	600/50-22.5
650/45-22.5 LS2 TT	T422 SB	150A8	16	150A2	157A2	650	1160	683	1189	539	3480	550	AG20.00	650/45-22.5
710/40-22.5 LS2 TT	T428 SB	151A8	16	151A2	158A2	710	1170	746	1179	540	3510	550	AG20.00	700/40-22.5
710/40-24.5 LS2 TT	T428 SB	163A8	20	163A2	170A2	710	1220	745	1230	570	3715	575	AG24.00	710/40-24.5
600/55-26.5 LS2 TT	T422 SB	165A8	20	165A2	172A2	600	1340	630	1373	625	4020	625	AG20.00	600/55-26.5
600/55-26.5 LS2 TT	T428 SB	165A8	20	165A2	172A2	600	1340	630	1374	625	4020	625	AG20.00	600/55-26.5
710/45-26.5 LS2 TT	T422 SB	163A8	18	163A2	170A2	710	1340	746	1357	625	4020	625	AG24.00	700/50-26.5
710/45-26.5 LS2 TT	T428 SB	163A8	18	163A2	170A2	710	1340	746	1357	625	4020	625	AG24.00	700/50-26.5
710/45-26.5 LS2 TT	T422 SB	168A8	20	168A2	175A2	710	1340	746	1357	625	4020	625	AG24.00	700/50-26.5
710/45-26.5 LS2 TT	T428 SB	168A8	20	168A2	175A2	710	1340	746	1357	625	4020	625	AG24.00	700/50-26.5
750/50-26.5 LS2 TT	T428 SB	174A8	20	174A2	181A2	750	1465	788	1476	675	4395	670	AG24.00	700/50-26.5
710/50-30.5 LS2 TT	T428 SB	173A8	20	173A2	180A2	710	1485	746	1522	700	4485	700	AG24.00	700/50-30.5
750/45-30.5 LS2 TT	T428 SB	173A8	20	173A2	180A2	750	1465	788	1497	700	4395	685	AG24.00	700/50-30.5/ 800/45-30.5
600/60-30.5 LS2 TT	T414 FS	153A8	14	153A2	160A2	600	1495	638	1545		4485	700	AG20.00	600/60-30.5
600/65-34 LS2 TT	T422 SB	157A8	14	157A2	164A2	600	1650	630	1691	775	4950	760	DW20A	600/65-34
710/55-34 LS2 TT	T422 SB	161A8	14	161A2	168A2	710	1650	746	1691	775	4950	760	DW24A	700/55-34
750/65-34 LS2 TT	T422 SB	169A8	16	169A2	176A2	750	1850	788	1896	875	5550	850	DW24A	30.5-32

Subject to technical amendments, printing errors and mistakes in text or illustrations. 05.23

Twin Forestry 422 The solution for increased accessibility



- Excellent traction without using any anti slide device
- The angle of the lugs gives extra pull force and brilliant accessibility
- The open tread pattern gives the best possible self-cleaning
- The large contact area gives the tyre a low ground bearing pressure

Twin Forestry 428 The solution for all-round service



- The wide, flat tire profile ensures excellent compatibility with tracks and chains
- The extra rubber reinforcement in the shoulder area reduces wear and tear from tracks and chains
- The pattern design allows good traction and self-cleaning
- The large contact area gives the tyre a low ground bearing pressure



Follow us



Yokohama TWS S.p.A.
Via Nazionale Tiburtina, 143 - 00019 Villa Adriana - Tivoli (RM), Italy
Phone: +39 0774 3841 – info.tws@yokohama-tws.com
www.trelleborg-tires.com

