



# **EMR 1025 Earthmover Radial Tires**

PREMIUM RADIAL PNEUMATIC

Protecting people protecting assets, Trelleborg's EMR 1025 all-season tire adds extra comfort and safety on ice and snow.

EMR 1025 offers both the comfort and robustness of the EMR range and delivers high performance year round as a commercial all-season tire.

Seasonal changeovers are no longer necessary.

# **Main Benefits**

- Premium damage protection and durability
- Provides control and perfect grip on ice and snow
- Seasonal changeovers are no longer necessary

## **Application**



### **Tire Features**









# **EMR 1025**

# PREMIUM RADIAL PNEUMATIC

### LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth [mm]	Service Description LI/SS Loader	Tire Load Capacity (kg) 10 (km/h)	Tire Pressure (bar)
17.5 R 25	L2	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	28	* 176 A2	7,100	4.50
20.5 R 25	L2	17.00/2.0-25 (17.00/1.7-25)	31	* 186 A2	9,500	4.50
23.5 R 25	L2	19.50/2.5-25	34	* 195 A2	12,150	4.50

 $<sup>^*/^{**}</sup>$  - Index of tire strength

#### **GRADER SERVICE**

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth [mm]	Service Description LI/SS Grader	Tire Load Capacity (kg) 40 (km/h)	Tire Pressure (bar)
14.00 R 24	G2	8.00TG-24 (SDC) 10.00VA-24 (SDC)	24	* 153 A8	3,650	3.75
17.5 R 25	G2	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	28	* 153 A8	3,650	3.00
20.5 R 25	G2	17.00/2.0-25 (17.00/1.7-25)	31	* 161 A8	4,625	3.00
23.5 R 25	G2	19.50/2.5-25	34	* 170 A8	6,000	3.00

<sup>\*/\*\* -</sup> Index of tire strength

## **NEW SIDEWALL PROTECTION**















