

Innovation to accelerate
your business.



Material Handling tire solutions.

Resilient tires

TRELLEBORG ELITE XP / TRELLEBORG M²

Premium tire designed for demanding material handling environments - Features the Pit Stop Line wear indicator for better planning.



TIRE SIZES				SPECIAL COMPOUNDS
3.00-4 ^[1]	21x8-9	6.00-15	400/60-15 ^[2]	MULTI PURPOSE
4.00-4 ^[1]	180/60-10	7.00-15	7.50-16	NON MARKING
4.00-8	200/50-10	7.50-15	9.00-20	ELECTRICALLY CONDUCTING
5.00-8	23x9-10	8.25-15	10.00-20	CUT RESISTANT
15x4½-8	6.50-10	28x9-15	11.00-20 ^[1]	CHEMICAL & RESISTANT
16x6-8	7.00-12	250-15	12.00-20	PRO TEX
17x7-8 ^[2]	23x10-12	280/50-15 ^[2]	355/50-20	PRO HD
18x7-8	27x10-12	300-15	12.00-24/10.00 ^[1]	PRO ENERGY
18x9-8 ^[2]	315/45-12	355/45-15 ^[2]	12.00-24/8.5 ^[1]	
140/55-9	23x5-13 ^[1]	355/50-15	14.00-24 ^[1]	
6.00-9	5.50-15	355/65-15	16.00-25 ^[1]	

[1] Only available in Elite XP [2] Only available in M²

TRELLEBORG PREMIA

Premium tire designed for demanding material handling environments.



TIRE SIZES			SPECIAL COMPOUNDS
15x4½-8	6.50-10	8.25-15	MULTI PURPOSE
5.00-8	200/50-10	28x9-15	NON MARKING
16x6-8	23x9-10	250-15	ELECTRICALLY CONDUCTING
18x7-8	7.00-12	300-15	CHEMICAL & RESISTANT
140/55-9	23x10-12	355/45-15	
6.00-9	27x10-12	355/50-15	
21x8-9	7.00-15	355/65-15	

MASTERSOLID /ORCA

Standard tire designed for applications that are not in constant use or that carry a lower load.



TIRE SIZES			SPECIAL COMPOUNDS
3.00-4	21x8-9	7.50-15	MULTI PURPOSE
4.00-8	6.50-10	8.25-15	NON MARKING
15x4½-8	200/50-10	28x9-15	
5.00-8	23x9-10	250-15	
16x6-8	7.00-12	300-15	
18x7-8	23x10-12	465/55-20 ^[1]	
140/55-9	27x10-12	355/65-15 ^[2]	
6.00-9	7.00-15		

[1] Only available in Mastersolid [2] Only available in Orca

ECOSOLID

Ecosolid is an entry-level solid tire option designed for use on forklifts in light-duty application.



TIRE SIZES		SPECIAL COMPOUNDS
15x4½-8	23x9-10	MULTI PURPOSE
5.00-8	7.00-12	
16x6-8	23x10-12	
18x7-8	27x10-12	
140/55-9	8.25-15	
6.00-9	28x9-15	
21x8-9	250-15	
6.50-10	300-15	
200/50-10	355/65-15	

Press On Solid Tires

* Full range of sizes available in the Trelleborg technical catalogue or on the website.

TRELLEBORG PRESS ON SOLID

Premium tire designed for demanding material handling environments.



POPULAR TIRE SIZES *

9x5x5	16x7x10½	21x6x15	28x10x22
10x4x6½	15x5x11¼	21x7x15	28x12x22
10½x5x6½	15x6x11¼	21x8x15	28x14x22
10½x7x6½	16¼x5x11¼	21x9x15	28x16x22
13x3½x8	16¼x6x11¼	22x7x16	40x12x30
13x4½x8	16¼x7x11¼	22x8x16	40x14x30
13x5x8	17x5x12	22x9x16	40x16x30
13½x5½x8	17x6x12	22x10x16	40x20x30
14x4½x8	18x5x12	22x12x16	
14x5x10	18x6x12	22x14x16	
15½x5x10	18x7x12	22x16x16	
16x5x10½	18x8x12	22x6x17¾	
16x6x10½	18x9x12	26x7x20	

SPECIAL COMPOUNDS



Pneumatic tires

TRELLEBORG TR-900

Premium radial tire designed for demanding material handling environments.



TIRE SIZES

5.00R8	250R15
6.00R9	300R15
6.50R10	10.00R20
7.00R12	12.00R20
7.00R15	12.00R24
8.25R15	14.00R24
28x9R15	16.00R25

SPECIAL COMPOUNDS

TRELLEBORG T-900

Premium bias tire designed for demanding material handling environments.



TIRE SIZES

5.00-8	7.00-15	9.00-20
18x7-8	7.50-15	10.00-20
6.00-9	8.25-15	11.00-20
6.50-10	28x9-15	12.00-20
23x9-10	250-15	12.00-24
7.00-12	300-15	14.00-24
23x10-12	355/65-15	
27x10-12	7.50-16	

SPECIAL COMPOUNDS

MITAS FL-08

Standard tire designed for applications that are not in constant use or that carry a lower load.



TIRE SIZES

4.00-8	6.50-10	8.15-15
5.00-8	23x9-10	250-15
15x4½-8	7.00-12	300-15
16x6-8	27x10-12	
18x7-8	23x5-13	
6.00-9	7.50-15	
21x8-9	8.25-15	

SPECIAL COMPOUNDS

* Pit Stop Line not available
† Special compound in development



Discover our website

Follow us

