

# Slangar STT Twinslangar



DIMENSION	VENTIL
<b>Ø15.3</b>	
280/60-15.5/11.0/60-15.3/11.5/60-15.3	TR15
<b>Ø15.5</b>	
350/70-15.5/400/60-15.5	TR15
400/60-15.5	TR15
<b>Ø17.5</b>	
350/60-17.5/400/55-17.5	TR15
<b>Ø22.5</b>	
400/55-22.5/400/60-22.5	TR218
500/45-22.5	TR218
500/60-22.5	TR218
600/50-22.5	TR218
<b>Ø26.5</b>	
400/60-26.5/400/65-26.5	TR218
500/60-26.5	TR218
600/55-26.5	TR218
700/50-26.5	TR218
800/40-26.5	TR218
<b>Ø30.5</b>	
600/55-30.5/600/60-30.5	TR218
700/50-30.5/800/45-30.5	TR218
<b>Ø34</b>	
600/65-34/710/55-34	TR218
<b>Ø38</b>	
600/55-38/600/60-38	TR218
650/60-38	TR218
700/65-38/750/65-38/710/70-38	TR218
<b>Ø54</b>	
5.00-54 TR77 RT	TR218