



EMR 1025 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

Protecting people protecting assets, Trelleborg's EMR 1025 all-season tire adds extra comfort and safety on ice and snow.

EMR 1025 offers both the comfort and robustness of the EMR range and delivers high performance year round as a commercial all-season tire. Seasonal changeovers are no longer necessary.

Main benefits

- · Excellent damage protection and durability
- · Perfect control and grip on ice and snow
- · Maximum productivity for all-seasons
- Robust casing to support eventual retreading*

Application



*Casing should be checked by a professional technician before retreading is permitted

Tire features









ALL-SEASON


ALL-STEEL RADIAL CONSTRUCTION

HIGH GRIP ON SNOW

EXCELLENT RIDE COMFORT

EMR 1025

PREMIUM RADIAL PNEUMATIC



TECHNICAL DATA - LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Loader	Tire Load Capacity (lbs) at 6 (mph)	Tire Pressure (psi)
17.5 R 25	L2	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	35	* 176 A2	15,656	65
20.5 R 25	L2	17.00/2.0-25 (17.00/1.7-25)	39	* 186 A2	20,948	65
23.5 R 25	L2	19.50/2.5-25	43	* 195 A2	26,791	65

^{*/** -} Index of tire strength

TECHNICAL DATA - GRADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Loader	Tire Load Capacity (lbs) at 25 (mph)	Tire Pressure (psi)
14.00 R 24	G2	8.00TG-24 (SDC) 10.00VA-24 (SDC)	30	* 153 A8	8,048	54
17.5 R 25	G2	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	35	* 153 A8	8,048	44
20.5 R 25	G2	17.00/2.0-25 (17.00/1.7-25)	39	* 161 A8	10,198	44
23.5 R 25	G2	19.50/2.5-25	43	* 170 A8	13,230	44

^{*/** -} Index of tire strength



Trelleborg Wheel Systems Americas, Inc. 107 Audubon Road, Building 2, Suite #205, Wakefield MA, 01880 www.trelleborg.com/en-us/wheels







