



Application



*Casing should be checked by a professional technician before retreading is permitted

EMR 1030 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability. The multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial casing and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for articulated dump truck, loader and grader applications, the EMR 1030 range is ideal for every kind of haulage and loading operations and extremely versatile in industries such as open pits, quarries, infrastructure development and site preparation.

Main benefits

- Excellent self-cleaning properties
- Low vibration
- Cut resistant compound
- Robust casing to support eventual retreading*

Tire features



TECHNICAL DATA - LOADER/TRANSPORT SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Loader/Transport	Tire Load Capacity (lbs) at 6 (mph)	Tire Pressure (psi)	Tire Load Capacity (lbs) at 31 (mph)	Tire Pressure (psi)
17.5 R 25	L3/E3	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	34	* 176 A2/157 B	15,656	65	9,096	51
20.5 R 25	L3/E3	17.00/2.0-25 (17.00/1.7-25)	43	** 193 A2/177 B	25,358	83	16,097	65
23.5 R 25	L3/E3	19.50/2.5-25	45	** 201 A2/185 B	31,973	83	20,396	65
26.5 R 25	L3/E3	22.00/3.0-25	53	** 209 A2/193 B	40,793	83	25,358	65
750/65 R 25	L3/E3	24.00/3.0-25	52	** 209 A2/190 B	40,973	91	23,373	62
29.5 R 25	L3/E3	25.00/3.5-25	55	** 216 A2/200 B	49,392	83	30,870	65

*/** - Index of tire strength

TECHNICAL DATA - GRADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Grader	Tire Load Capacity (Ibs) at 25 (mph)	Tire Pressure (psi)
17.5 R 25	G3+	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	34	* 153 A8	8,048	44
20.5 R 25	G3+	17.00/2.0-25 (17.00/1.7-25)	43	* 161 A8	10,198	44
23.5 R 25	G3+	19.50/2.5-25	45	* 170 A8	13,230	44
26.5 R 25	G3+	22.00/3.0-25	53	* 178 A8	16,538	44
750/65 R 25	G3+	24.00/3.0-25	52	* 178 A8	16,538	47

+ Not marked as grader on the mold */** - Index of tire strength



Trelleborg Wheel Systems Americas, Inc. 107 Audubon Road, Building 2, Suite #205, Wakefield MA, 01880 www.trelleborg.com/en-us/wheels

> facebook.com/TrelleborgConstruction youtube.com/TrelleborgConstruction

> > F 🖸





03.21