



# EMR 1042 Earthmover Radial Tires

### PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability. The multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial casing and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for articulated dump trucks and loader applications, the EMR 1042 tire is optimal for haulage operations in open pits, quarries, infrastructure development and site preparation.

## **Main benefits**

- Superior traction
- Long tire life due to deep tread
- Excellent ride comfort
- Sidewall rubber ring guard protection
- Robust casing to support eventual retreading\*

### **Application**



\*Casing should be checked by a professional technician before retreading is permitted

### **Tire features**









ALL-STEEL RADIAL CONSTRUCTION


REINFORCED CASING

MULTI SURFACE

EXCELLENT RIDE COMFORT



# PREMIUM RADIAL PNEUMATIC



# TECHNICAL DATA - TRANSPORT/LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Transport/Loader	Tire Load Capacity (Ibs) at 6 (mph)	Tire Pressure (psi)	Tire Load Capacity (lbs) at 31 (mph)	Tire Pressure (psi)
23.5 R 25	E4/L4	19.50/2.5-25	64	** 185 B/201 A2	31,973	83	20,396	65
26.5 R 25	E4/L4	22.00/3.0-25	68	** 193 B/209 A2	40,793	83	25,358	65
29.5 R 25	E4/L4	25.00/3.5-25	73	** 200 B/216 A2	49,392	83	30,870	65

<sup>\*/\*\* -</sup> Index of tire strength



