



EMR 1030 V Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability.

The R1 tread pattern delivers control and perfect grip when it's needed the most, whether on soil, fields and mud.

The strong radial casing and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption. EMR 1030 V is especially designed for loaders and dozer agriculture application.

Main benefits

- Excellent self-cleaning properties
- Low vibration
- Cut resistant compound
- Robust casing to support eventual retreading*

Application



*Casing should be checked by a professional technician before retreading is permitted

Tire features







CASING



MULTI SURFACE



EMR 1030 V

PREMIUM RADIAL PNEUMATIC

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread depth [32nd]	Service description LI/SS Loader	Tire load capacity (lbs) 6 (mph)	Tire pressure (psi)
20.5 R 25	L3	17.00/2.0-25 (17.00/1.7-25)	45	** 193 A2	25,358	83.00

** - Index of tire strength







