



# EMR 1051 Earthmover Radial Tires

# PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability. The multi-surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial casing and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for loaders, the EMR 1051 range is the best solution for intensive loading applications in industries such as open pits, quarries, infrastructure development and site preparation.

#### **Main benefits**

- Optimal traction
- Excellent tire life due to deep tread
- Cut resistant compound
- Sidewall rubber ring guard protection
- Robust casing to support eventual retreading\*

# **Application**



#### \*Casing should be checked by a professional technician before retreading is permitted

#### **Tire features**









ALL-STEEL RADIAL

REINFORCED

MULTI

**EXCELLENT** 

# **EMR 1051**

# PREMIUM RADIAL PNEUMATIC



# **TECHNICAL DATA – LOADER SERVICE**

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth [32nd]	Service Description LI/SS Loader	Tire Load Capacity (Ibs) at 6 (mph)	Tire Pressure (psi)
20.5 R 25	L5	17.00/2.0-25 (17.00/1.7-25)	88	** 193 A2	25,353	83
23.5 R 25	L5	19.50/2.5-25	96	** 201 A2	31,973	83
26.5 R 25	L5	22.00/3.0-25	107	** 209 A2	40,793	83
29.5 R 25	L5	25.00/3.5-25	116	** 216 A2	49,392	83

<sup>\*/\*\* -</sup> Index of tire strength

Trelleborg Wheel Systems Americas, Inc. 107 Audubon Road, Building 2, Suite #205, Wakefield MA, 01880 www.trelleborg.com/en-us/wheels

facebook.com/TrelleborgConstruction



Trelleborg Wheel Systems Americas, Inc. 107 Audubon Road, Building 2, Suite #205, Wakefield MA, 01880 www.trelleborg.com/en-us/wheels













