








Protecting people protecting assets.

Delivering the smoothest ride in the Brawler range. Trelleborg's Brawler HPS Soft Ride tires are designed to perform in tough recycling, scrap, and waste environments. The Soft Ride compound combined with Brawler's unique elliptical sidewall apertures delivers higher shock absorption and reduced vibration, ensuring the best possible protection for operators and equipment. Brawler HPS Soft Ride offers both the toughness of a traditional solid tire and the ride comfort of a foam filled pneumatic tire.


Vibration & Comfort - Dynamic Test

TESTED TO ISO 5008



Deflection – Static Test

DEFORMATION (MM) UNDER VARIABLE LOAD



Solid Tire

Load (lbs)



Brawler HPS Soft Ride.







ANTI VIBRATION CONSTRUCTION

Enhanced driver comfort



CUT RESISTANT COMPOUND

Damage protection



ELLIPTICAL APERTURES

Increased deflection



ULTRA DEEP TREAD

Extended service life

Why choose Soft Ride?



MAXIMUM VALUE

Reduced operating cost per hour



MAXIMUM UPTIME

Increased productivity, maintenance free



INCREASED SAFETY

Reduced driver exposure to vibration



REDUCED IMPACT

Protecting people, protecting assets

Brawler HPS Soft Ride

PREMIUM OTR SOLID



HPS Solidflex

HPS Solidflex

Smooth

HPS SOLIDFLEX TRACTION

Tire Size	Rim Size	Overall diameter (in)	Section width (in)	Tread depth (32nd)	Load capacity 6 mph (lbs)
17.5-25	14.0-25	52.8	17.6	195	19,410
20.5-25	17.0-25	58.9	20.7	237	26,795
23.5-25	19.5-25	64.2	23.9	272	33,775
26.5-25	22.0-25	67.5	28.3	298	40,335
29.5-25	25.0-25	72.6	30.0	333	49,690

HPS SOLIDFLEX SMOOTH

Tire Size	Rim Size	Overall diameter (in)	Section width (in)	Tread depth (32nd)	Load capacity 6 mph (lbs)
17.5-25	14.0-25	52.8	17.6	195	19,410
20.5-25	17.0-25	58.9	20.7	237	26,795
23.5-25	19.5-25	64.2	23.9	272	33,775
26.5-25	22.0-25	67.5	28.3	298	40,335
29.5-25	25.0-25	72.6	30.0	333	49,690
18.00-33	13.0-33	72	18.0	272	26,455

HPS SMOOTH

Tire Size	Rim Size	Overall diameter (in)	Section width (in)	Tread depth (32nd)	Load capacity 6 mph (lbs)
20.5-25	17.0-25	58.9	20.7	237	35,737
23.5-25	19.5-25	64.2	23.9	272	45,029
26.5-25	22.0-25	67.5	28.3	298	53,771
29.5-25	25.0-25	72.6	30.0	333	66,249

Notes: Tread depth on smooth tires indicates wearable rubber. All Brawler™ HPS tires are available as either an assembly or as tire only.



Trelleborg Wheel Systems Americas, Inc. 107 Audubon Road, Building 2, Suite #205, Wakefield MA, 01880 www.trelleborg.com/en-us/wheels

> facebook.com/TrelleborgConstruction youtube.com/TrelleborgConstruction





