



Earthmover Radial Tires

PREMIUM CONSTRUCTION PNEUMATIC

EMR 1045

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability while the multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for rigid dumper applications, our EMR 1045 tire is the best choice for haulage operations in open pits and quarries.

Applications



Tire Features



PREMIUM CONSTRUCTION PNEUMATIC

EMR 1045

TRANSPORT SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Transport	Tire Load Capacity (Ibs) at 31 (mph)	Tire Pressure (PSI)
18.00 R 33	E4	13.00/2.5-33	68	** 191 B	24,030	94

^{*/**} – Index of tire strength

Main Benefits

- Supreme traction and stability
- Excellent tire life due to deep tread
- Reduced fuel consumption

