


New 480/80R50 TM600 The ideal solution for muddy terrains with increased road performance

The original tread design of the new Trelleborg TM600 has been developed for customers needing a tire that covers the gap between the R1-W and R2 tread types. The new TM600 is the ideal solution for producers looking for versatility in their operations needing a tire for heavy, wet field operations and light road use.









SIZE	Tread patter		SW 0 inches inc		SLF					Rim		Type Tube		
480/80R50 159A8 (159B)	TM600	TM600 1		80.5 -		-	- 975			DW15B		SS	-	
1	Weight lbs 474.07													
psi	9	12	15	i	17	20	23		29	35	41	42	44	
bar	0.6	0.8	1		1.2	1.4	1.6		2	2.4	2.8	2.9	3	
MAX. LOAD Ib														
30 S	4540	5210	599	0 6	760	7530	830	0	8970	9650				
25 S	4540	5210	599	0 6	760	7530	830	0	8970	9650				
20 S	4860	5580	640	0 7	230	8060	888	0	9600	10330				
5 LT S	6110	7020	806	0 9	100	10140	1118	30	12090	13000	14210	14500	16420	
5 HT S	4860	5580	640	0 7	230	8060	888	0	9600	10330				

Design Data



