

Treleboge High Knuring. The perfect match.





Trelleborg High Knurling - THK

Trelleborg High Knurling - THK handles high stress and extreme torque, enabling tractors to work at maximum efficiency and productivity. Together with Trelleborg Extra Large tires, THK represents a system that meets all requirements.

The use of tractors with the latest generation of engines that provide powerful traction, increases the strain on tires, rims and their interaction.

The latest tests that have been performed prove that Trelleborg High Knurling - THK, answers our customers' toughest requirements. New technology has delivered an advanced knurling design where the height of the profile has almost doubled, providing maximum performance at high speed and torque. In addition, by coating the bead seat of the rim with friction paint, the grip is significantly improved so that tire slippage at extreme torque is prevented.



The knurling has been increased by 50% compared to the standard version. This, combined with the special black paint, maximises the friction characteristics of rim when the tire is fitted.

Trelleborg High Knurling is available for all the sizes with standard knurling, from 24" up to 54".





Trelleborg Wheel Systems Italia S.p.A. Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy Phone: +39 0774 384701 - Fax: +39 0774 384702 www.trelleborg.com/wheels