



BUREAU
VERITAS

Bureau Veritas Certification

Trelleborg Antivibration Solutions Germany GmbH

Berliner Straße 17, 16727, Velten, Germany

This is a multi-site certificate, additional site(s) are listed on the next page(s)

Bureau Veritas Certification Holding SAS - UK Branch certifies that the Management System of the above organisation has been audited and found to be in accordance with the requirements of the management system standards detailed below

ISO 9001:2015

Scope of certification

Design, Development, Manufacturing and Sales of vibration control products.

Original cycle start date:	19-02-2024
Expiry date of previous cycle:	NA
Certification / Recertification Audit date:	NA
Certification / Recertification cycle start date:	19-02-2024
Subject to the continued satisfactory operation of the organisation's Management System, this certificate expires on:	18-02-2027

Certificate No.: SE009806

Version: 1

Issue date: 16-02-2024



0008

Signed on behalf of BVCH SAS UK Branch

Certification Body Address: 5th Floor, 66 Prescott Street, London, E1 8HG, United Kingdom

Local Office: Fabriksgatan 13, Gothenburg, SE-41250, Sweden

Further clarifications regarding the scope and validity of this certificate, and the applicability of the management system requirements, please call: +46 31 606500

UKAS Certificate Template Multi Site Rev.4.1

28 Aug 2023





BUREAU
VERITAS

Bureau Veritas Certification

Trelleborg Antivibration Solutions Germany GmbH

ISO 9001:2015

Scope of certification

Site Name	Site Address	Site Scope
Trelleborg Antivibration Solutions Germany GmbH	Berliner Straße 17, 16727, Velten, Germany	Design, Development, Manufacturing and Sales of vibration control products.
Trelleborg Antivibration Solutions Switzerland AG	Soodstraße 57, 8134, Adliswil, Switzerland	Sales, Development and Testing of rubber-metall parts for antivibration solutions.

Certificate No.: SE009806

Version: 1

Issue date: 16-02-2024



Signed on behalf of BVCH SAS UK Branch

Certification Body Address: 5th Floor, 66 Prescott Street, London, E1 8HG, United Kingdom

Local Office: Fabriksgatan 13, Gothenburg, SE-41250, Sweden

Further clarifications regarding the scope and validity of this certificate, and the applicability of the management system requirements, please call: +46 31 606500

UKAS Certificate Template Multi Site Rev.4.1

28 Aug 2023

