

KLENET

KLENET PROCESSING EQUIPMENT

TRELLEBORG

KLENET - WP 10 BAR

95 °C - Made in France



Applications

Washdown and cleaning in food processing industries, canneries, dairies, slaughterhouses, etc.

Advantages

- Very good resistance to high temperatures.
- Smooth for easy handling with light-coloured, non-marking cover.
- Excellent resistance of the cover compound to animal and vegetable grease.
- Contains no phthalate.

Technical description

Inner tube: food grade quality oil resistant NBR, white, smooth.

Reinforcement: synthetic textile.

Cover: oil and weather resistant NBR/PVC, blue, smooth.

Temperature range: -20 °C to +95 °C.

Standard/Approval

EU regulations No. 1935/2004, 2023/2006.

FDA regulation No. 21 CFR 177.2600.

German legislation: BfR recommendation XXI cat. 3.

French legislation.

All relevant migrations tests (France and FDA) were performed by the French institute of Poitiers (IANESCO) and confirmed compliant.

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

Complementary information

Not recommended with washdown guns.

ID mm	OD mm	Working pressure bar	Bursting pressure bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock or min. order m		
13	±0.5	21,4	±0.7	10.0	30	80	0.3	20	0060962	•
								40	0060961	•
								60	0060952	4620
								120	0060953	•
16	±0.7	25	±0.8	10.0	30	95	0.38	20	0060964	•
								40	0060963	•
								60	0060954	1440
								120	0060955	•
19	±0.7	28,4	±0.8	10.0	30	115	0.48	20	0060966	•
								40	0060965	•
								60	0060956	•
								25	±1.0	35
25	±1.0	35	±1.1	10.0	30	155	0.62	40	0060967	•
								60	0060957	1020

• Upon availability.

* Tolerance on length: ± 1 % (ISO 1307 Standard)

Branding