



BSPP

V04/09/2016

TECHNICAL INFORMATION

- Thread according NF EN ISO 228-1
- Shank according to EN 14420-2
- Material: stainless steel 316/1.4401
- Working pressure: 25 bar
- Temperature: 100 °C
- PTFE flat thread seal



RELATED PRODUCTS

- UTS ferrules
- Safety clamps
- Flat thread seal

www.trelleborg.com/fluidhandling

Contact: robin.lallemand@trelleborg.com



BSPP SS316

Female - PTFE gasket

| Part number | Thread size (mm) | DN Hose (mm) | Stock |
|-------------|------------------|--------------|-------|
| 5103269 | 1/2" | 13 | ✓ |
| 5103270 | 3/4" | 19 | ✓ |
| 5103271 | 1" | 25 | ✓ |
| 5103272 | 1" 1/4 | 32 | ✓ |
| 5103273 | 1" 1/2 | 38 | ✓ |
| 5103274 | 2" | 50/51 | ✓ |
| 5103275 | 2" 1/2 | 63 | ✓ |
| 5103276 | 3" | 75-76 | ✓ |
| 5103277 | 4" | 100/102 | ✓ |

BSPP SS316

Male

| Part number | Thread size (mm) | DN Hose (mm) | Stock |
|-------------|------------------|--------------|-------|
| 5103293 | 1/2" | 13 | ✓ |
| 5103294 | 3/4" | 19 | ✓ |
| 5103295 | 1" | 25 | ✓ |
| 5103296 | 1" 1/4 | 32 | ✓ |
| 5103297 | 1" 1/2 | 38 | ✓ |
| 5103298 | 2" | 50/51 | ✓ |
| 5103299 | 2" 1/2 | 63 | ✓ |
| 5103300 | 3" | 75-76 | ✓ |
| 5103301 | 4" | 100/102 | ✓ |

NEW

SAFE & RELIABLE CONNECTION

Same safety collar

Nut retaining by cliclips