



# BSPP

### TECHNICAL INFORMATION

- Thread according NF EN ISO 228-1
- Shank according to EN 14420-2
- Material: stainless steel 316/1.4401
- Working pressure: 25 bar
- Temperature: 100°C
- PTFE flat thread seal



### RELATED PRODUCTS

- UTS ferrules
- Safety clamps
- Flat thread seal

[www.trelleborg.com/fluidhandling](http://www.trelleborg.com/fluidhandling)



BSPP SS316			
Female - PTFE gasket			
Part number	Thread size	DN Hose (mm)	Stock
5103269	1/2"	13	✓
5103270	3/4"	19	✓
5103271	1"	25	✓
5103272	1" 1/4	32	✓
5103273	1" 1/2	38	✓
5103274	2"	50/51	✓
5103275	2" 1/2	63	✓
5103276	3"	75-76	✓
5103277	4"	100/102	✓

BSPP SS316			
Male			
Part number	Thread size	DN Hose (mm)	Stock
5103293	1/2"	13	✓
5103294	3/4"	19	✓
5103295	1"	25	✓
5103296	1" 1/4	32	✓
5103297	1" 1/2	38	✓
5103298	2"	50/51	✓
5103299	2" 1/2	63	✓
5103300	3"	75-76	✓
5103301	4"	100/102	✓

