

Hose Support

SAFETY & HANDLING PRODUCTS

ADVANTAGES

- Improve handling operations
- Use: fixed or mobile
- Keep and protect the hose structure

COMPLEMENTARY INFORMATION

- Material: urethane
- Sling material: polyester UV Resistant
CE certified slings: rated capacity of 5000 kg
- Maximum temperature: 93.3 °C

| SAFETY & HANDLING PRODUCTS | | | | |
|----------------------------|-------------|---------|---------------------|-------|
| Hose support | Part number | ID hose | Rated Capacity (kg) | Stock |
| | 5105144 | 3" | 648.00 | ✓ |
| | 5105145 | 4" | 648.00 | ✓ |
| | 5105146 | 6" | 2500.00 | ✓ |
| | 5105147 | 8" | 3888.00 | ✓ |
| | 5105148 | 10" | 4860.00 | ✓ |

www.trelleborg.com/fluidhandling

Contact: tes.serviceclients@trelleborg.com



Hose Support

SAFETY & HANDLING PRODUCTS

ADVANTAGES

- Improve handling operations
- Use: fixed or mobile
- Keep and protect the hose structure

COMPLEMENTARY INFORMATION

- Material: urethane
- Sling material: polyester UV Resistant
CE certified slings: rated capacity of 5000 kg
- Maximum temperature: 93.3 °C

| SAFETY & HANDLING PRODUCTS | | | | | |
|----------------------------|-------------|---------|---------------------|--------------|-------|
| Hose support | Part number | ID hose | Rated Capacity (kg) | Price list € | Stock |
| | 5105144 | 3" | 648.00 | 380.00 | ✓ |
| | 5105145 | 4" | 648.00 | 425.00 | ✓ |
| | 5105146 | 6" | 2500.00 | 750.00 | ✓ |
| | 5105147 | 8" | 3888.00 | 1275.00 | ✓ |
| | 5105148 | 10" | 4860.00 | 1900.00 | ✓ |

www.trelleborg.com/fluidhandling

Contact: tes.serviceclients@trelleborg.com

