



TRI-CLAMP (SMS Norm & ISO Norm)

TECHNICAL INFORMATION

- Shank according to EN 14420-2
- Material: stainless steel 316L/1.4404
- Working pressure: 16 bar
- Ra ≤ 0.5 on request
- Electropolishing on request

RELATED PRODUCTS

- UTS ferrules
- Safety clamps
- Clamp
- Gasket: FPM/EPDM/NBR/SILICONE

www.trelleborg.com/fluidhandling



TRI-CLAMP SS316L

SMS norm

Part number	OD Ferrule (mm)	DN Hose (mm)	Stock
5103375	50.5	25	✓
5103376	50.5	38	✓
5103377	64.0	50/51	✓
5103378	77.5	63	✓
5103379	91.0	75/76	✓
5103380	119.0	100/102	✓

TRI-CLAMP SS316L

ISO norm

Part number	OD Ferrule (mm)	DN Hose (mm)	Stock
5103382	50.5	19	☎
5103383	50.5	25	☎
5103384	50.5	32	☎
5103385	64.0	32	☎
5103386	64.0	38	☎
5103387	77.5	50/51	☎
5103388	91.0	63	☎
5103389	106.0	75/76	☎
5103390	130.0	100/102	☎

