



GUILLEMIN

V04/09/2016

TECHNICAL INFORMATION

- GUILLEMIN according to NF EN 14420-8
- Shank according to EN 14420-2
- Material: stainless steel 316/1.4401
- Working pressure: 16 bar -
*Except for Ø 150 mm
- Temperature: -20°C +65°C
- CSM gasket

RELATED PRODUCTS

- UTS ferrules
- Safety clamps
- Spanner
- Other gaskets: NBR/EPDM/PTFE/FPM

www.trelleborg.com/fluidhandling

Contact: robin.lallemand@trelleborg.com

GUILLEMIN				SS316
Part number	Coupling size	DN Hose (mm)	A	Stock
5103343	25	25	37.5	✓
5103344	32	32	42.5	✓
5103345	40	38	55	✓
5103346	50	50/51	69	✓
5103347	65	63	84	✓
5103348	80	75/76	104	✓
5103349	100	100/102	124	✓
5103893*	150	152	193	✓

