


ALCODIAL



FOOD & BEVERAGE



APPLICATIONS

Particularly adapted for alcohol transfer up to 99%.

Suitable for all drinks: wine, beer, brandies and spirits, fruit juice, milk, etc. Designed for equipement of:

- production plants (distillery, spirit and liqueur producer, etc),
- loading or unloading bays from road and rails tankers.

ADVANTAGES

- Very flexible and anti-kinking resistant hose.
- UPE inner tube accepting alcohol temporary stagnation without risk of
- migration.
- Odourless and tasteless inner tube.
- Non-marking, abrasion resistant cover.
- Contains no phthalate.

COUPLING/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

Please refer to our cleaning guidelines, available upon request and from our website.

TECHNICAL DESCRIPTION

Inner tube	food grade UPE, white, smooth.
Reinforcement	synthetic textile with embedded steel helix
Cover	NR, blue, fabric impression.
Temperature range	-30°C => +80°C

STANDARD/APPROVAL

EU regulations No. 1935/2004, 2023/2006,	EU
FDA regulation No. 21 CFR 177.1520.	FDA
All relevant migrations tests (France and FDA)	
French legislation.	RF



гоо г	& BEVERAGE	AI	LCODIAL				
ID (MM)	OD (MM)	WORKING PRESSURE (BAR)	BURSTING PRESSURE (BAR)	BENDING RADIUS (MM)	WEIGHT (KG/M)	LENGTH (M)	ARTICLE NUMBER
25.0	36.0	10	30	55	0.80	20	5501078
25.0	36.0	10	30	55	0.80	40	5501079
32.0	43.0	10	30	70	0.93	20	5501080
32.0	43.0	10	30	70	0.93	40	5501081
38.0	49.0	10	30	84	1.12	20	5501082
38.0	49.0	10	30	84	1.12	40	5501083
51.0	62.5	10	30	112	1.43	20	5501084
51.0	62.5	10	30	112	1.43	40	5501085
63.0	74.5	10	30	139	2.08	20	5501086
63.0	74.5	10	30	139	2.08	40	5501087
70.0	83.0	10	30	154	2.61	20	5501088
70.0	83.0	10	30	154	2.61	40	5501089
76.0	89.0	10	30	167	2.86	20	5501090
76.0	89.0	10	30	167	2.86	40	5501091

Tolerance on length: -2%/0%

