



WELDING END (BW & SMS)

V04/09/2016

TECHNICAL INFORMATION

- Shank according to EN 14420-2

RELATED PRODUCTS

- UTS ferrules
- Safety clamps
- All welding couplings

www.trelleborg.com/fluidhandling

Contact: robin.lallemand@trelleborg.com



BW		SS316	
Part number	A (mm)	DN Hose (mm)	Stock
5103245	21.3	13	✓
5103246	26.7	20	✓
5103247	33.7	25	✓
5103248	42.2	32	✓
5103249	48.3	38	✓
5103250	60.3	50/51	✓
5103251	76.1	63	✓
5103252	88.9	75/76	✓
5103253	114.3	100/102	✓
5103254	139.7	125	✓
5103255	168.3	152	✓
5103256	219.1	204	✓

BW		CARBON STEEL	
Part number	A (mm)	DN Hose (mm)	Stock
5103257	21.3	13	✓
5103258	26.7	20	✓
5103259	33.7	25	✓
5103260	42.2	32	✓
5103261	48.3	38	✓
5103262	60.3	50/51	✓
5103263	76.1	63	✓
5103264	88.9	75/76	✓
5103265	114.3	100/102	✓
5103266	139.7	125	✓
5103267	168.3	152	✓
5103268	219.1	204	✓

SMS		SS316	
Part number	A (mm)	DN Hose (mm)	Stock
5103234	15	13	✓
5103235	20	20	✓
5103236	25	25	✓
5103237	32	32	✓
5103238	38	38	✓
5103239	51	50/51	✓
5103240	63	63	✓
5103241	76	75/76	✓
5103242	104	100/102	✓
5103243	125	125	✓
5103244	150	152	✓