

Tailored buoyancy solutions

Njord DBM (Distributed Buoyancy Module)

In floating production scenarios, pipelines such as flexible risers, cables and umbilicals are often required to be held subsea in specific geometric configurations designed to prevent over utilization of the system. Although numerous configurations have been developed and implemented over the years, one favored method is to attach discreet buoyancy modules to the outside of the pipeline. The buoyant load must not migrate or degrade over the design life of the product.

Njord DBMs (Distributed Buoyancy Modules) are typically used between a subsea structure and a surface vessel or platform. The clamping solution allows the Njord DBMs to be fitted at any point along the length of the pipeline.



The two main functions of the Njord DBMs are to provide uplift and maintain location along the riser. The uplift is generated by a two part buoyancy component. A clamp securely attaches the assembly to the desired location on the riser. The buoyancy segments are assembled to mechanically lock around the clamp and are secured with circumferential straps.

To provide the project performance at every level, the buoyancy system can be adjusted to operate in seawater depths from surface to 6,000m and beyond.



Benefits:

- Reduces top tension loads
- Maintain project specific riser configuration
- Fast, efficient and safe offshore installation procedure
- Compliant systems aimed at encapsulating large flowline tolerances and expansions/contractions
- Extensive subsea track record
- Industry qualified materials and geometry
- Comprehensive document and drawing package



Contact Us

Trelleborg Offshore delivers innovative and reliable offshore solutions that maximize business performance to meet your needs. Our dedicated and highly skilled staff are always on hand to provide seamless process support from initial idea, through to delivery and beyond.



Brazil: +55 22 2106 4040
China: +86 137 9287 9241
France: +33 3 44 23 03 50
Norway: +47 32 23 20 00
Singapore: +65 6265 0955
United Kingdom: +44 1695 712 000
United States: +1 832 456 8300



Email: Offshore@trelleborg.com



TRELLEBORG

WWW.TRELLEBORG.COM/OFFSHORE