

Trelleborg DrainPacker Patch Kit

01

Configuration pack:	No. 01
Main pipe:	4"
Rehabilitation length:	2 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234462

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

02

Configuration pack:	No. 02
Main pipe:	4"
Rehabilitation length:	4 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234468

Contents:

- 1 PCS Trelleborg Silicate Resin Type W,
Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener,
Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

03

Configuration pack:	No. 03
Main pipe:	6"
Rehabilitation length:	2 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234463

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,00 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,50 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

04

Configuration pack:	No. 04
Main pipe:	6"
Rehabilitation length:	4 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234469

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

05

Configuration pack:	No. 05
Main pipe:	8"
Rehabilitation length:	2 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234464

Contents:

- 1 PCS Trelleborg Silicate Resin Type W,
Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener,
Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

06

Configuration pack:	No. 06
Main pipe:	8"
Rehabilitation length:	4 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234470

Contents:

- 2 PCS Trelleborg Silicate Resin Type W,
Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener,
Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

07

Configuration pack:	No. 07
Main pipe:	8"
Rehabilitation length:	5 ft
Resin type:	Silicate S
Pot time:	32 min, 68 °F
Cure time:	260 min, 59 °F

230100

Contents:

- 1 PCS Trelleborg Silicate Resin Type S, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 2 PCS Trelleborg Silicate Resin Type S, Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

08

Configuration pack:	No. 08
Main pipe:	8"
Rehabilitation length:	5 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234502

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 2 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

09

Configuration pack:	No. 09
Main pipe:	10"
Rehabilitation length:	2 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234465

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 0,34 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,16 litre
- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

10

Configuration pack:	No. 10
Main pipe:	10"
Rehabilitation length:	4 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234471

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 2 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

11

Configuration pack:	No. 11
Main pipe:	12"
Rehabilitation length:	2 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234466

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

12

Configuration pack:	No. 12
Main pipe:	12"
Rehabilitation length:	4 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234472

Contents:

- 3 PCS Trelleborg Silicate Resin Type W,
Bottle, content 1,34 litre
- 3 PCS Trelleborg Resin Hardener,
Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

13

Configuration pack:	No. 13
Main pipe:	15"
Rehabilitation length:	2 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234467

Contents:

- 2 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

14

Configuration pack:	No. 14
Main pipe:	15"
Rehabilitation length:	4 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234473

Contents:

- 4 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 4 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

15

Configuration pack:	No. 15
Main pipe:	8"
Rehabilitation length:	7 ft
Resin type:	Silicate W
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234716

Contents:

- 1 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,00 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,50 litre
- 3 PCS Trelleborg Silicate Resin Type W, Bottle, content 1,34 litre
- 3 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

16

Configuration pack:	No. 16
Main pipe:	6"
Rehabilitation length:	4 ft
Resin type:	Silicate S
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

232961

Contents:

- 1 PCS Trelleborg Silicate Resin Type S, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 1 PCS Trelleborg Silicate Resin Type S, Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

17

Configuration pack:	No. 17
Main pipe:	8"
Rehabilitation length:	4 ft
Resin type:	Silicate S
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

233102

Contents:

- 2 PCS Trelleborg Silicate Resin Type S,
Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener,
Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Trelleborg DrainPacker Patch Kit

18

Configuration pack:	No. 18
Main pipe:	10"
Rehabilitation length:	4 ft
Resin type:	Silicate S
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

233103

Contents:

- 1 PCS Trelleborg Silicate Resin Type S, Bottle, content 0,67 litre
- 1 PCS Trelleborg Resin Hardener, Bottle, content 0,33 litre
- 2 PCS Trelleborg Silicate Resin Type S, Bottle, content 1,34 litre
- 2 PCS Trelleborg Resin Hardener, Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+ 1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula



Made in the EU. Please read our Safety Data Sheets.

Trelleborg DrainPacker Patch Kit

19

Configuration pack:	No. 19
Main pipe:	4"
Rehabilitation length:	4 ft
Resin type:	Silicate S
Pot time:	15 min, 68 °F
Cure time:	115 min, 59 °F

234817

Contents:

- 1 PCS Trelleborg Silicate Resin Type S,
Bottle, content 1,34 litre
- 1 PCS Trelleborg Resin Hardener,
Bottle, content 0,66 litre
- 1 PCS Trelleborg Glass Fiber Mat CRF+
1050 g/m² for 3 layers
- 2 PCS Protective foil
- 1 PCS Ground sheet
- 2 PCS Safety glasses
- 1 PCS Binding wire
- 5 PCS Disposable gloves (pair)
- 8 PCS Cable ties
- 2 PCS Spatula

