

epros®SteamGen Modelle / epros®SteamGen Types

Übersicht / Overview

| Technische Daten Technical Features | | Modellbezeichnung SteamGen Type | | | | | | | | |
|--|-------------|------------------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| | | epros® SteamGen M50 | epros® SteamGen M150 | epros® SteamGen M200 | epros® SteamGen M300 | epros® SteamGen M400 | epros® SteamGen M500 | epros® SteamGen M600 | epros® SteamGen M700 | epros® SteamGen M800 |
| Dampfleistung Steam production | kg/h | 50 | 150 | 200 | 300 | 400 | 500 | 600 | 700 | 800 |
| Heat Potential | kcal/h | 29.000 | 90.000 | 120.000 | 180.000 | 240.000 | 300.000 | 360.000 | 420.000 | 480.000 |
| Wärmeleistung | kW | 34 | 105 | 140 | 211 | 281 | 352 | 422 | 492 | 562 |
| Arbeitsdruck Pressure | bar | 12 | 5 | 5 | 5 | 5 | 5 | 5 | 5 | 5 |
| Max. Ölverbrauch Max. Oil-consumption | kg / h | 3 | 9,5 | 13 | 19,6 | 20 | 32,6 | 42,8 | 45,7 | 52,1 |
| Breite (A) Width | mm | 450 | 600 | 750 | 850 | 850 | 1400 | 1400 | 1400 | 1500 |
| Höhe (B) Height | mm | 1000 | 1300 | 1800 | 2000 | 2000 | 2000 | 2000 | 2000 | 2000 |
| Tiefe (C) Depth | mm | 750 | 1100 | 2400 | 2400 | 2400 | 2700 | 2700 | 2700 | 3000 |
| Gewicht Weight | kg | 300 | 370 | 700 | 880 | 900 | 950 | 1000 | 1050 | 1200 |
| Kamin Chimney | Ø | 120 | 120 | 160 | 160 | 200 | 250 | 300 | 300 | 300 |
| Elektrischer Anschlusswert Power supply | A | 5 | 6 | 6 | 6 | 6 | 6 | 6 | 6 | 6 |
| Betriebsspannung Operating voltage | V/Hz | 230 / 50 | 230 / 50 | 400 / 50 | 400 / 50 | 400 / 50 | 400 / 50 | 400 / 50 | 400 / 50 | 400/50 |
| Max. Wasserverbrauch Max. water consumption | l/h | 50 | 160 | 220 | 330 | 440 | 550 | 660 | 770 | 880 |
| Aufheizzeit (ca.) Heat-up time (approx.) | Min | 10 | 10 | 10 | 15 | 15 | 15 | 15 | 15 | 15 |
| Dampfauslass Steam Outlet | Zoll / inch | 1 | 1 | 1 | 2 | 2 | 2 | 2 | 2 | 2 |
| Dampfschläuche Steam hoses | mm | 25 | 25 | 25 | 50 | 50 | 50 | 50 | 50 | 50 |