

Rollin[®]Type500


Key performance

- Consistent throw length, uniform nip pressure, easy washup
- The best adhesive in the market to avoid creeping and lifting
- Clean and easy removal from the cylinder
- Improved blanket lifetime

MAIN APPLICATION

Business Forms and Labels

Rollin Type500 available in 2 ply, 0,95 - 1,05 mm thickness



Rollin Type500



The product at a glance

INK COMPATIBILITY	UV
PRINTING SURFACE COLOUR	Green
THICKNESS (mm)	0,95 - 1,05
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	350
SURFACE ROUGHNESS (Ra micron)	0,8
ADDITIONAL INFORMATION	
APPLICATIONS	Adhesive

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**