



vulcan® Hybrid Black

Key Performance

- Special top face for both conventional & UV inks
- Very good half tone reproduction and high printing quality
- Excellent paper smash resistance
- Reduced edge mark

MAIN APPLICATION

Sheetfed

Vulcan Hybrid Black is available in 3 ply, 1,95 mm thickness



Vulcan Hybrid Black



The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Black
THICKNESS (mm)	1,95
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	275
SURFACE ROUGHNESS (Ra micron)	0,8
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>170
ADDITIONAL INFORMATION	
APPLICATIONS	Suitable for alternating printing (conventional & UV inks)

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**