



Printec® 205

Key Performance

- Ideal for 3-piece can printing
- Extreme high printing quality
- Specifically designed for UV inks

MAIN APPLICATION

Metal Decorating

Printec 205 is available in 4 ply (1,97 mm) thickness



Printec 205

✓ The product at a glance

INK COMPATIBILITY	UV
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,97
AVERAGE LOAD VALUE N/cm² @ 0,20 mm Indentation	150
SURFACE ROUGHNESS (µm)	0,70 to 1,30
ELONGATION (%)	< 2
TENSILE STRENGTHS (kgf/cm)	> 71.5
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
APPLICATIONS	Metal Decorating

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printing@trelleborg.com**