

# Rollin® Polycell Plus

## Key performance

- High printing quality
- Improved load consistency batch to batch
- Easy blanket set up on machine
- Implements all benefits of the **Dynatech System**:
  - Better vibration absorption
  - Less gears streaking marks
  - Higher paper smash resistance,
  - Blanket consistency
  - Excellent reboundability

## MAIN APPLICATION

Commercial Sheetfed,  
Packaging

**Rollin Polycell is available in  
3-ply, 1,96 mm thickness.**

## ✓ The product at a glance

<b>INK COMPATIBILITY</b>	Hybrid
<b>PRINTING SURFACE COLOUR</b>	Light Green
<b>THICKNESS (mm)</b>	1,96
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,23 mm Indentation</b>	250
<b>SURFACE ROUGHNESS (Ra micron)</b>	0,8
<b>ELONGATION (%)</b>	<0,9
<b>TENSILE STRENGTHS (N/mm)</b>	>60
<b>WATER &amp; SOLVENT PROTECTION</b>	No
<b>NEW TECHNOLOGY</b>	Dynatech System
<b>ADDITIONAL INFORMATION</b>	
<b>APPLICATIONS</b>	Suitable also for packaging printing

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printing@trelleborg.com](mailto:printing@trelleborg.com)**