



vulcan[®] Pack

Key performance

- Ideal for 4-color presses
- Excellent half tone reproduction and ink transfer coverage
- High edge marking resistance
- Increased blanket lifetime

MAIN APPLICATION

Metal Decorating,
Packaging

**Vulcan Pack is available in
3 ply, 1,95 mm thickness.**



Vulcan Pack

✓ The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,95
AVERAGE LOAD VALUE N/cm² @ 0,23 mm Indentation	350
SURFACE ROUGHNESS (Ra micron)	0,8
ELONGATION (%)	<0,9
TENSILE STRENGTHS (N/mm)	>60
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
DESIGN	Specifically designed for metal decorating applications

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printing@trelleborg.com**