





Key performance

- Excellent top face resistance
- Stable paper feed on large format presses
- High stability and versatility
- Long blanket lifetime
- High print quality

MAIN APPLICATION

Heatset, Coldset

Printec 600 is available in 3/4-ply, 1,71/1,96 mm thickness

Printec 600



The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Light Blue
THICKNESS (mm)	1,71/1,96
AVERAGE LOAD VALUE N/cm2 @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	0,8
FEED FEATURES	Slightly Positive
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>60
WATER & SOLVENT PROTECTION	Yes
ADDITIONAL INFORMATION	
APPLICATIONS	Premium choice for heatset

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**