


Key Performance

- Suitable for all kind of sheetfed machines
- Conventional inks compatibility
- Ideal for commercial sheetfed applications
- Resistance to frequent format changes
- Provides quick release
- Excellent image detail and overall high print quality
- Harder face to prevent edge cutting
- Reduced blanket usage and smashing
- Reduced pilling of the face

MAIN APPLICATION

Sheetfed

Printec 864 is available in 1,98 mm thickness



Printec 864

✓ The product at a glance

INK COMPATIBILITY	Conventional
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,98
AVERAGE LOAD VALUE N/cm² @ 0,20 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	1
WATER & SOLVENT PROTECTION	No
ADDITIONAL INFORMATION	
APPLICATIONS	Sheetfed

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION
PLEASE REFER TO YOUR SALES MANAGER
OR EMAIL US AT: printingsm@trelleborg.com**